

Date Updated: 2018-03-15

● Yes, — No, ▽ In Progress

Model No.	CamProExpress 64 v1.0.15.77753 Service Version 2.1.3.77705	Campro Professional v2.0.5.79057	Campro Mobile iOS V3.0.16	Campro Mobile Android V3.0.7	Campro VMS 3.3.0.61122	Luxriot EVO 1.7.1	Synology NVR DSM-6.1.3-15152 or higher Surveillance Station 8.1 or higher	Qnap NAS Surveillance Station 5.1.1.3(4).4.20171031 / NVR QVR 5.1.1.20171031	AirLive View	Asustor NVR ADM 2.6 (Surveillance Center v2.6)	Digiever NVR Firmware version 2.1.x.64 or later	IPCAM Viewer V5.8.5 (3rd Party)	DigiFort V7.0.0.0	Milestone Xprotect Enterprise 2014	NUUO Main Console V6.0	Dahua NVR V2.610.000.0.6	Axon Next V3.6
VD-2128 v3_C0	—	—	—	—	—	Onvif	▽	▽	—	Onvif	●	—	Onvif	Onvif	—	Onvif	Onvif
BU-3128 v3_C0	—	—	—	—	●	●	▽	●	—	Onvif	●	—	Onvif	Onvif	—	Onvif	Onvif
VD-2028 v3_C013S1	—	—	—	—	●	●	●	●	—	Onvif	●	—	Onvif	Onvif	—	Onvif	Onvif
SmartCube 300W v1.81	●	●	●	●	●	—	●	●	—	●	—	●	Onvif	Onvif	—	Onvif	Onvif
BC-5010 v2.37	●	●	●	●	●	—	●	●	—	▽	—	●	●	Onvif	—	Onvif	Onvif
BC-5010 IVS v2.36	●	●	●	●	●	—	●	●	—	▽	—	●	●	Onvif	—	Onvif	Onvif
MD-3025 v2.51	●	●	●	●	●	●	●	●	—	●	●	●	●	Onvif	—	Onvif	Onvif
MD-3025-IVS v2.51	●	●	●	●	●	●	●	●	—	●	●	●	●	Onvif	—	Onvif	Onvif
BU-3026 v2.44	●	●	●	●	●	—	●	●	—	●	—	●	●	Onvif	—	Onvif	Onvif
BU-3026-IVS v2.44	●	●	●	●	●	—	●	●	—	●	—	●	●	Onvif	—	Onvif	Onvif
BU-3028 v1.62	●	●	●	●	●	—	●	●	—	▽	—	●	●	Onvif	—	Onvif	Onvif
BU-3028-IVS v1.62	●	●	●	●	●	—	●	●	—	▽	—	●	●	Onvif	—	Onvif	Onvif
FE-201DM A1.0.1_0911	●	●	●	—	▽	—	—	—	—	—	—	—	—	Onvif	Onvif	Onvif	Onvif
FE-501DM A1.0.1_0911	●	●	●	—	●	—	—	—	—	—	—	—	—	Onvif	Onvif	Onvif	Onvif
FE-501OD A1.0.1_0911	●	●	●	—	●	—	—	—	—	—	—	—	—	Onvif	Onvif	Onvif	Onvif
SD-3030 vk20151015NSZ	●	●	●	▽	●	●	▽	●	—	▽	●	▽	▽	▽	▽	▽	Onvif
CU-720PIR v6.E.2.10554	●	●	●	●	▽	—	●	—	●	—	—	●	●	Onvif	Onvif	Onvif	Onvif
CW-720 v6.E.2.10554	●	●	●	●	▽	—	●	—	●	—	—	●	●	Onvif	Onvif	Onvif	Onvif
POE-100HD-ICR v5.0.2.6495	●	●	●	●	▽	—	●	—	—	—	—	●	●	—	—	—	—
OD-325HD v5.0.2.7232	●	●	●	●	—	—	●	—	—	—	—	●	●	—	●	—	—
OD-325HD-2.5MM v5.0.2.7232	●	●	●	●	—	—	●	—	—	—	—	●	●	—	●	—	—
POE-100HD v5.0.2.6495	●	●	●	●	▽	—	—	—	—	—	—	●	●	—	●	—	—
POE-200HD-4MM v5.0.2.7232	●	●	●	●	▽	—	—	—	—	—	—	●	●	—	●	—	—
POE-250HD v5.0.2.6495	●	●	●	●	▽	—	—	—	—	—	—	●	●	—	●	—	—
OD-2050HD v6.D.2.9659	●	●	●	●	▽	—	—	—	—	—	●	●	●	Onvif	Onvif	Onvif	Onvif
IP-200PHD-24 v6.B.2.9031	●	●	●	●	▽	—	●	—	●	—	●	●	●	Onvif	Onvif	Onvif	Onvif
OD-2060HD v6.C.2.10104	●	●	●	●	●	—	—	—	—	—	●	●	●	Onvif	—	Onvif	Onvif
OD-2025HD v6.D.2.9659	●	●	●	●	▽	—	—	—	—	—	●	●	●	Onvif	Onvif	Onvif	Onvif
PoE-2600HD v6.C.2.10104	●	●	●	●	—	—	—	—	—	—	●	●	●	Onvif	—	Onvif	Onvif
WN-2600HD v6.C.2.10104	●	●	●	●	—	—	—	—	—	—	●	●	●	Onvif	—	Onvif	Onvif
WN-200HD v6.B.2.9031	●	●	●	●	—	—	—	—	—	—	●	●	●	Onvif	Onvif	Onvif	Onvif
POE-5010HD v4.0	●	●	●	●	—	—	—	—	—	—	—	●	●	Onvif	—	Onvif	Onvif
FE-200CU v2.3.0716	●	●	●	●	—	—	—	—	—	—	—	●	—	—	—	—	—
FE-200DM v2.3.0716	●	●	●	●	—	—	—	—	—	—	—	●	—	—	—	—	—
FE-200VD v2.3.1024	●	●	●	●	—	—	—	—	—	—	—	●	—	—	—	—	—
BU-3025 v1.03.13	●	●	●	●	—	—	—	—	—	—	●	—	—	Onvif	Onvif	Onvif	Onvif
BU-2015 v1.03.28	●	●	●	●	●	●	●	●	—	—	●	●	●	Onvif	Onvif	Onvif	Onvif
WN-150CAM v.LM.1.6.18P3	●	●	●	●	—	—	—	—	—	—	—	—	—	—	—	—	—
POE-200CAMv2 v.LM.1.6.18	●	●	●	●	—	—	—	—	—	—	—	—	—	—	—	—	—
POE-260CAM v.LM.1.6.18	●	●	●	●	—	—	—	—	—	—	—	—	—	—	—	—	—
WL-2600CAM v.LM.1.6.18	●	●	●	●	—	—	—	—	—	—	—	—	—	—	—	—	—
MD-720 v.M2.1.6.04C036_T1	●	●	●	●	●	—	●	—	—	●	●	●	●	Onvif	Onvif	Onvif	Onvif
BU-720 v.M2.1.6.05C021	●	●	●	●	—	—	—	—	—	●	●	●	●	Onvif	Onvif	Onvif	Onvif
DM-720 v.M2.1.6.04C036_T1	●	●	●	●	—	—	—	—	—	●	—	●	●	Onvif	Onvif	Onvif	Onvif
POE-280HD v.MG.1.6.03P10_TM7	●	●	●	●	●	—	—	—	—	—	—	—	—	Onvif	Onvif	Onvif	—
WL-350HD v.MG1.6.03C5	●	●	●	●	—	—	—	—	—	●	—	—	—	—	—	—	—
SD-2020 vk20140819NSA	●	●	●	●	●	—	Onvif	●	—	—	●	●	●	Onvif	Onvif	Onvif	Onvif
BU-3025V2 v1.03.18	●	●	●	●	—	—	—	—	—	●	●	●	●	Onvif	—	Onvif	Onvif
CW-720IR v6.L.0.15708	●	●	●	●	—	—	Onvif	—	—	—	—	●	●	●	Onvif	Onvif	Onvif
CU-720IR v6.L.0.15708	●	●	●	●	—	—	Onvif	●	—	—	—	●	●	●	Onvif	Onvif	Onvif

The latest information are marked in red
 IPCAM viewer: MD-3025, BU-3026 connect with BC-5010 Model name
 DigiFort: CW-720IR, CU-720IR connect with CW-720 Model name
 Asustor: BU-3028 connect with BU-3026 Model name